



Introducing the latest generation of phototherapy systems, whose new modern design and the power of LED light at 7 different wavelengths achieve incredibly superior results in the most common skin treatments.

- **Approved by the FDA**
- **UV-free light therapy**
- **Professional level LED light**
- **No recovery time needed**

Its modern technology uses the power of light emitting diodes to provide cells with new energy, improving their performance to achieve the desired therapeutic effect. Its high-performance LEDs at different wavelengths allow you to treat multiple skin conditions faster and more effectively:

- Reduces fine lines and wrinkles.
- Reduces redness.
- Tightens the facial contour, neck, eye area, hands and décolleté.
- Increases collagen production creating younger looking skin.
- Speeds up wound healing.
- Stimulates hair growth.
- Reduces muscle and joint pain.
- Relieves spasms and muscle tension.

The LumiMax can also be used in combination with other procedures, minimizing the side effects associated to the treatments and maximizing results by:

- Shortening the recovery time.
- Reducing pain.
- Avoiding scar formation.
- Reducing inflammation, hyperpigmentation, edema and bruising.

♦ An advanced LED light therapeutic system that works at a cellular level, creating an amazing regenerating and repairing effect.

Safe, painless, and more effective. No matter the skin type or color.



NO  
CHEMICALS




NO PAIN



NON  
INVASIVE



NO SIDE  
EFFECTS



NO RECOVERY  
TIME

# The most powerful LED light therapy system for a deep and visible skin transformation

**7** cell-specific wavelengths  
to repair, tighten and rejuvenate



LOW LEVEL LIGHT THERAPY

**Blue light at 462 nm:** Effectively fights acne thanks to its purifying, anti-bacterial and anti-inflammatory properties.

**Red light at 622 nm:** Stimulates fibroblasts to improve collagen production, smoothing the appearance of wrinkles.

**Green light at 522nm:** Penetrates the subcutaneous layers to reduce melanin production in the skin surface, effectively treating skin discoloration and hyperpigmentation.

**Yellow light at 423 nm:** Its effect on the skin is similar to the red light's, effectively treating redness caused by sun exposure and stimulating blood flow.

**Violet light at 400 nm:** This combination of red light and blue light eliminates acne causing bacteria, reduces the inflammation associated with acne, and diminishes the appearance of residual scars.

**Cyan light at 490 nm:** Combines the properties of green light and blue light to fight acne and simultaneously reduce hyperpigmented spots.

**White light at 400-700 nm:** Penetrates deep into the tissues to speed up skin metabolism and help reduce the signs of aging.



- The LumiMax is ideal in combination with other treatments, as it optimizes their effect thanks to the properties of LED light.

All the programs are compatible with other cosmetic procedures, including:

- Botox and dermal fillers.
- Laser hair removal.
- IPL and chemical peels.
- Surgical treatments such as laser resurfacing.
- They can also be used before or after surgery to stimulate wound healing and reduce recovery time.

Using an advanced ergonomic LED light panel with 7 proven wavelengths, the LumiMax can accommodate to all body parts to maximize light absorption, offering more and better results in only a few minutes per treatment.

#### **Dramatically reduces the signs of aging**

The red light energy at 622 nm stimulates the production of new collagen fibers to reduce the signs of aging and sun damage, creating a more beautiful, smoother and younger looking skin from the very first day.

#### **Effectively fights acne and rosacea**

By using blue light at 462nm, or a combination of blue and red light, the LumiMax effectively treats rosacea and achieves significant improvements in the appearance of acne, destroying the bacteria that causes it and regenerating the affected tissues.

#### **Stimulates hair growth**

The use of LED light effectively treats hair loss and prevents further loss.

**LED light therapy**  
for amazing results that  
you can see and feel



♦ Its improved speed and power make the LumiMax an excellent addition to your center by offering multiple advantages over other systems in its category.

**Proven safety**

The light energy deeply penetrates the tissues to naturally stimulate cell regeneration, achieving noticeable changes without pain, side effects or recovery time.

**Maximum efficiency**

Its extra luminous diodes offer 100 times the power to rejuvenate and revitalize, while the infrared light technology offers additional benefits to accelerate post-surgical healing and recovery.

**Easy to use**

Incorporates a practical articulated panel, on-screen help with language selection and treatment protocol menu for easy operation.

**More profitable**

Its superior technology allows you to achieve faster results, increasing client satisfaction and offering much more lucrative treatments.

**Versatile designs** 

Its state-of-the-art articulated panel allows you to do a wide variety of treatments by a commodating to both curved and flat areas, addressing the specific needs of each patient.

♦ The widest range of face and body solutions in on single last generation device.

Applications	Technologies
<ul style="list-style-type: none"><li>• Rejuvenation</li><li>• Fine lines and wrinkles</li><li>• Tightening</li><li>• Post-surgery</li><li>• Acne and acne with irritation</li><li>• Redness and outbreaks of redness</li><li>• Photo-aging</li><li>• Scars and stretch marks</li><li>• Hair growth</li><li>• Spasms and muscle tension</li><li>• Muscle and joint pain</li></ul>	<ul style="list-style-type: none"><li>• Blue light at 462 nm</li><li>• Yellow light at 423 nm</li><li>• Red light at 622 nm</li><li>• Green light at 522 nm</li><li>• Violet light at 400 nm</li><li>• Cyan Light at 490 nm</li><li>• White light at 400-700 nm</li></ul>

**Estetique USA**

2145 N Commerce Parkway  
Weston, FL 33326 USA

Tel: 1 954-442-6595  
Toll Free: 1 888 214 3856

**Estetique Mexico**

Avenida Homero, 1339 Piso 6  
Colonia Polanco IV Sección  
Miguel Hidalgo, CDMX CP  
11550 Mexico

Tel: 52 55 4634 0496  
52 55 5161 2483

E-mail: sales@estetique.com  
ventas@estetique.com

Web: www.estetique.com

Más productos de Estetique

**RejuveMax®**  
COLLAGEN LIGHT SYSTEM

**LipoMax® RF**  
FACE | BODY

**DermaMax® RF**  
RF MICRONEEDLING SYSTEM

**DermaMax®**  
HYDRODERMABRASION SYSTEM

**LumiMax® PL**  
LASER SYSTEM

**LumiMax® CO2**  
CO2 LASER SYSTEM

With its new powerful combination of 7 different wavelengths, the LumiMax offers highly effective solutions to a wider range of treatments.

The LumiMax comes with an articulated panel that incorporates extra super luminous diodes to repair the tissues without pain, chemicals, thermal damages or side effects.

It also offers manual mode for PDT (Phot Dynamic Therapy) or personalized programs, as well as a variety of pre-programmed protocols designed to treat multiple skin problems.

The practical articulated panel is designed to accommodate perfectly to both flat and curved surfaces, maximizing the effect of facial treatments and adjusting to different body areas to treat conditions such as back acne, stretch marks on the abdomen and photo-aging on the hands and the décolleté, among others,

**Features:**

- High intensity biomedical LED light
- 100% UV-free, eliminating the risk of damaging the skin.
- Safe and with no risk of burns.
- Non-invasive, non-chemical, pain-free and with no side effects.
- Ideal for over skin type.
- Does not require recovery time or aftercare.
- Does not require the therapist to be constantly present.
- Low treatment costs.
- Easy operation and simple maintenance.
- Articulated panel for face and body treatments.
- Large 65cm x 22 cm treatment area for face and body
- 10" touchscreen.
- Multiple language selection.
- Moveable station.
- Electronically adjustable height.

**Especificaciones Técnicas:**

- |                     |  |
|---------------------|--|
| • Light spectrum    | Blue light 462 nm<br>Yellow light 423 nm<br>Red light 622 nm<br>Green light 522 nm<br>Violet light 400 nm<br>Cyan light 490 nm<br>White light 400-700 nm |
| • Power supply      | 100-240 VAC 50/60 HZ   |
| • Power consumption | 120 W  |
| • Weight            | 55 Kg  |
| • Work mode         | Continuous, pulsed, automatic  |
| • Dimensions        | 53 X 49 X 127 cms  |

